

SYSTEM-V

Components and Accessories at a Glance

		VP 9005	4540	VP 6005	4465
Base Boards + Accessories					
4472	Base Board 45 x 50 cm	○	●	○	
4413	Base Board 50 x 60 cm	●	○	○	
4414	Base Board 60 x 80 cm	○	○	○	
5508	Base Frame	○	○	○	
Columns + Accessories					
	Column w/o weight compensation, 1 m	○	●	○	
4474	Column with weight compensation, 1 m	●	○	○	
4475	Column with gear rack and fine drive, 1 m	○	○	○	
4476	Column with gear rack, 1 m	○	○	○	
4408	Column with gear rack, 1.20 m	○	○	○	
4409	Column with weight compensation, 1.50 m	○	○	○	
4412	Wall Mount	○	○	○	
4455	Extension Arm	○	○	○	
Head Lower Part + Accessories					
4568 *	Enlarger Head Lower Part	●	●	○	
4423	Lens Holder Ring up to 50 mm	●	●	–	
4424	Lens Holder Ring 60 - 105 mm	●	●	–	
Enlarger Heads + Accessories					
4541 *	B & W Head, up to 6 x 9 cm	●	●	○	
4453	Transformator	–	–	○	
4356 *	Opal Lamp, 75 W	●	●	○	
4459	Halogen Cold-Light Mirror Lamp	–	–	○	
Condensers					
4443 *	Double Condenser for 24 x 36 mm	○	○	○	
4542 *	Double Condenser up to 6 x 6 cm	○	●	○	
4449 *	Double Condenser up to 6 x 9 cm	●	○	–	
Compound Negative Carrier System					
4583 *	Compound Negative Carrier	●	●	–	
4584 *	Compound Negative Carrier 7 x 7 cm	○	○	–	
4486	Pair of Negative Masks 24 x 36 mm	○	●	○	
4491	Pair of Negative Masks 24,5 x 36,5 mm	○	○	○	
4431	Pair of Negative Masks 4,5 x 6 cm	○	○	○	
4485	Pair of Negative Masks 6 x 6 cm	○	○	○	
	Format Mask 6 x 7 cm	●	○	○	
4436	Pair of Negative Masks 6 x 7 cm	○	○	○	
4487	Glass Inserts, Anti-Newton	○	○	○	
4490	Glass Inserts, flat glass	○	○	○	
4433	Glass Inserts, AN glass/flat glass	●	○	○	
4435	Inserts, Negative Mask 24x36, AN-glass	○	○	○	
4434	Inserts, AN-glass/Format Mask 6 x 6 cm	○	●	○	
4432	Inserts, AN-glass/Format Mask 6 x 7 cm	○	○	○	
4489	Negative Mask for 5 x 5 cm slides	○	○	○	
4492	Panorama pair of masks 24 x 66 mm	○	○	○	
4494	Inserts for „do it yourself“ cut	○	○	○	
More Accessories					
4495 *	Filter Holder	●	○	○	
4448 *	Filter Drawer 85 x 85 mm	●	●	○	
	Dust Hood	●	●	○	

- belongs to standard equipment
- Combination possible, partly in connection with other components
- Combination not possible or not useful respectively
- * Can be used also for enlarger VP 350 (4401)

Almost all SYSTEM-V components of the previous enlarger generation can be used with the latest models with the following exceptions:

4442 Double Condenser for 6 x 6 cm	Combination not possible
4444 Colour Head	can be used for sizes up to 6 x 7 cm
4445 Multigrade Head	can be used for sizes up to 6 x 7 cm
4446 B & W Head	can be used for sizes up to 6 x 7 cm
4483 Compound Negative Carrier	Combination not possible
4484 Compound Neg. Carr., 7 x 7 cm	Combination not possible

KAISER[®]

FOTOTECHNIK

Slide Copying:

The compound negative carrier 4583 doesn't suit on the old colour head 4444 in upside-down-position. On the other hand the old compound negative carrier can be used on the colour head 4544 in upside-down-position.

Converting into copy stand:

The enlargers of the latest device generation can be converted into a copy stand with the components of the repro system R1.